

User assembly of other units, using:
 Body-contacts assemblies: see page 74
 Combined sub-assemblies: see page 80

Control and signaling units

Harmony XB5 plastic

Multiple-headed pushbuttons, spring return



XB5AL73415



ZB5AA7121



ZB5AL7341



XB5AW73731B5



ZB5AW7A1721



ZB5AW7A3741

Double-headed pushbuttons (1)

Screw clamp terminal connections (Schneider Electric anti-loosening system)

Shape of head	Description	Type of contact	Caps (2)		Reference	Weight kg/lb
			Marking	Background color		
		NO				
		NC				

Complete units

	1 flush push, black 1 projecting push, red	1	1	White "I"	Green	XB5AL73415	0.053/0.117
				White "0"	Red		

Heads only

	2 flush push, black			Unmarked	White	ZB5AA7120	0.023/0.051
				Unmarked	Black		
				Black "I"	White	ZB5AA7121	0.023/0.051
				White "0"	Black		
				Unmarked	Green	ZB5AA7340	0.023/0.051
				Unmarked	Red		
				Black "→"	White	ZB5AA7213	0.023/0.051
				White "←"	Black		
				White "I"	Green	ZB5AA7341	0.023/0.051
				White "0"	Red		
	1 flush push, black 1 projecting push, red			Without cap (3)		ZB5AA79	0.023/0.051
				Unmarked	Green	ZB5AL7340	0.023/0.051
				Unmarked	Red		
				White "I"	Green	ZB5AL7341	0.023/0.051
				White "0"	Red		

Double-headed pushbuttons with 1 white central pilot light block (1)

Screw clamp terminal connections (Schneider Electric anti-loosening system)

Shape of head	Description	Type of contact	Caps	Marking	Background color	Pilot light voltage V	Reference	Weight kg/lb
		NO						
		NC						

Complete units

	1 flush push, black 1 projecting push, red 1 central pilot light block, white	1	1	White "I"	Green	24	XB5AW73731B5	0.066/0.146
				White "0"	Red	120		
						240		

Heads only (5)

	2 flush push, black 1 central pilot light, clear (4)			Unmarked	White	ZB5AW7A1720	0.023/0.051
				Unmarked	Black		
				Black "I"	White	ZB5AW7A1721	0.023/0.051
				White "0"	Black		
				Unmarked	Green	ZB5AW7A3740	0.023/0.051
				Unmarked	Red		
				White "I"	Green	ZB5AW7A3741	0.023/0.051
				White "0"	Red		
				Black "↑"	Green	ZB5AW7A1724	0.023/0.051
				White "↓"	Red		
				Black "+"	White	ZB5AW7A1715	0.023/0.051
				Black "-"	White		
				Without cap (3)		ZB5AW7A9	0.023/0.051
	1 flush push, black 1 projecting push, red 1 central pilot light, clear (4)			Unmarked	Green	ZB5AW7L3740	0.023/0.051
				Unmarked	Red		
				White "I"	Green	ZB5AW7L3741	0.023/0.051
				White "0"	Red		

(1) Recommended maximum number of contacts constituting the body (fixing collar and contact) associated with the head, see page 20.

(2) These caps are factory assembled and cannot be removed (risk of damage).

(3) Caps to be ordered separately, see page opposite.

(4) Color of centrally positioned pilot light determined by the color of the LED incorporated in the body sub-assembly.

(5) Only for use with bodies comprising a light source with integral LED.

User assembly of other units, using:
Body-contacts assemblies: see page 74
Combined sub-assemblies: see page 80

Control and signaling units Ø Harmony XB5 plastic Multiple-headed pushbuttons, spring return



XB5AA731327



ZB5AA73133



ZB5AA71124



ZBA7235



ZBA7331



ZBA7432



ZBA709

Triple-headed pushbuttons ^{(1) (2)}

Screw clamp terminal connections (Schneider Electric anti-loosening system)

Shape of head	Description	Type of contact	Caps ⁽³⁾		Reference	Weight kg/lb
			Marking	Background color		
		NO				
		NC				
		NO				

Complete units

	2 flush push, black, 1 central projecting push, marked "Stop" in white	1	1	1	White "I"	Green	XB5AA731327	0.063/0.139
					White "II"	Green	XB5AA711237	0.063/0.139

Heads only

	2 flush push, black, 1 central projecting push, red marked "Stop" in white				White "I"	Green	ZB5AA73132	0.023/0.051
					White "II"	Green		
					White "↔"	Green	ZB5AA73133	0.023/0.051
					White "⇌"	Green		
					White "↑"	Green	ZB5AA73134	0.023/0.051
					White "↓"	Green		
					White "+"	Green	ZB5AA73135	0.023/0.051
					White "-"	Green		
					Black "+"	White	ZB5AA71115	0.023/0.051
					Black "-"	White		
					Black "↔"	White	ZB5AA71123	0.023/0.051
					White "↔"	Black		
					Black "↑"	White	ZB5AA71124	0.023/0.051
					White "↓"	Black		
					White "↑"	Black	ZB5AA72124	0.023/0.051
					White "↓"	Black		
					Without cap ⁽⁴⁾		ZB5AA791	0.023/0.051

Specific accessories for multiple-headed pushbuttons

Description	Marking	Background color	Sold in lots of	Reference	Weight kg/lb
Caps only for clip-on mounting ⁽⁵⁾ on: - ZB5AA79 double-headed pushbuttons - ZB5AW7A9 double-headed pushbuttons + central pilot light block - ZB5AA791 triple-headed pushbuttons	Unmarked	White	10	ZBA71	0.010/0.022
	"I" Black		10	ZBA7131	0.010/0.022
	"↑" Black		10	ZBA7134	0.010/0.022
	"+" Black		10	ZBA7138	0.010/0.022
	Unmarked	Black	10	ZBA72	0.010/0.022
	"O" White		10	ZBA7232	0.010/0.022
	"+" White		10	ZBA7233	0.010/0.022
	"↓" White		10	ZBA7235	0.010/0.022
	"I" White		10	ZBA7237	0.010/0.022
	Unmarked	Green	10	ZBA73	0.010/0.022
	"I" White		10	ZBA7331	0.010/0.022
	"+" White		10	ZBA7333	0.010/0.022
	"↓" White		10	ZBA7335	0.010/0.022
	"II" White		10	ZBA7336	0.010/0.022
	Unmarked	Red	10	ZBA74	0.010/0.022
	"O" White		10	ZBA7432	0.010/0.022
	Unmarked	Yellow	10	ZBA75	0.010/0.022
	Unmarked	Blue	10	ZBA76	0.010/0.022
Silicone boots for 2 flush push ⁽⁶⁾	—	Clear	10	ZBA708	0.055/0.121
Silicone boots for 3 pushes ⁽⁶⁾	—		10	ZBA709	0.055/0.121
Silicone boots for 1 flush push and 1 projecting push ⁽⁶⁾	—		10	ZBA710	0.055/0.121

⁽¹⁾ Recommended maximum number of contacts constituting the body (fixing collar and contact) associated with the head, see page 20.

⁽²⁾ Not compatible with high power switching contacts and contacts for printed circuit board.

⁽³⁾ These caps are factory assembled and cannot be removed (risk of damage).

⁽⁴⁾ Caps to be ordered separately, see accessories on this page.

⁽⁵⁾ Can be clipped-in at 90° steps, through 360°.

⁽⁶⁾ Can be replaced without dismantling the head.